

AD HR Series

High Rejection Seawater RO Elements

The AD HR Series, family of proprietary thin film reverse osmosis membrane elements, is characterized by an excellent sodium chloride rejection. AD HR series is selected when high quality permeate is demanded from seawater that is relatively high in TDS.

AD HR series new membrane chemistry provides excellent rejection characteristics when operated at seawater operating conditions (pressures exceeding 800psi (5,516kPa) and elevated seawater temperatures.

Table 1: Element Specification

Membrane	Thin-film membrane (TFM*)
----------	---------------------------

Model	Average permeate flow gpd (m ³ /day) ^{1,2}	Average NaCl rejection ^{1,2}	Minimum NaCl rejection ^{1,2}	Minimum Boron Rejection ²
AD-90	1500 (5.7)	99.75%	99.3%	93.0%
AD-365	6000 (22.7)	99.75%	99.3%	93.0%
AD-400, 34	6500 (24.6)	99.75%	99.3%	93.0%
AD-440	7100 (26.9)	99.75%	99.3%	93.0%

¹Average salt rejection after 24 hours operation. Individual flow rate may vary +25%/-15%.

²Testing conditions: 32,000mg/l NaCl & 5mg/l boron solution at 800psi (5,516kPa) operating pressure, 77°F (25°C), pH 8.0 and 7% recovery.

Model	Active area ft ² (m ²)	Outer wrap	Part number
AD-90	90 (8.4)	Fiberglass	3056651
AD-365	365 (33.9)	Fiberglass	3056652
AD-400, 34	400 (37.2)	Fiberglass	3056654
AD-440	440 (40.9)	Fiberglass	3056655

Table 2: Operating and CIP parameters

Typical Operating Pressure	800psi (5,516kPa)
Typical Operating Flux	7-11GFD (12-19LMH)
Maximum Operating Pressure	1,200psi (8,274kPa)
Maximum Temperature	Continuous operation: 122°F (50°C) Clean-In-Place (CIP): 122°F (50°C)
pH range	Optimum rejection: 7.0-7.5, Continuous operation 4.0-11.0, Clean-In-Place (CIP): 2.0-11.5
Maximum Pressure Drop	Over an element: 12 psi (83 kPa) Per housing: 50 psi (345 kPa)
Chlorine Tolerance	1,000+ ppm-hours, dechlorination recommended
Feedwater³	NTU < 1 SDI < 5

³SDI is measured on a non-linear scale using a 0.45 micron filter paper. Additionally, finer colloids, particulates and microorganisms that pass through the filter paper and not measured in the SDI test, will potentially foul the RO element. For performance consistency and project warranty, please use Winflows projection software and consult your Filters with Membranes representative.



Find a contact near you by visiting www.gewater.com and clicking on "Contact Us".

* Trademark of General Electric Company; may be registered in one or more countries.

©2014, General Electric Company. All rights reserved.

Figure 1a: Element Dimensions Diagram – Male




Figure 1b: Element Dimensions Diagram – Female




Table 3: Dimensions and Weights

Model ¹	Type	Dimensions, inches (cm)			Boxed Weight lbs (kg)
		A	B ²	C	
AD-90	Male	40.0 (101.6)	0.75 (1.90)	3.9 (9.9)	9 (4)
AD-365	Female	40.0 (101.6)	1.125 (2.86)	7.9 (20.1)	35 (16)
AD-400, 34	Female	40.0 (101.6)	1.125 (2.86)	7.9 (20.1)	35 (16)
AD-440	Female	40.0 (101.6)	1.125 (2.86)	7.9 (20.1)	35 (16)